

TS35 MPC 1725 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

Version	Rail, TS 35 x 7.5, TS 35, Width: 98 mm, without slot, with slot, Steel, galvanized, chromium-plated
Order No.	8000037607
Type	TS35 MPC 1725 VER
GTIN (EAN)	4050118653199
Qty.	20 items

TS35 MPC 1725 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	98 mm	Width (inches)	3.8583 inch
Net weight	22 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Installation advice	Direct mounting	Standards	DIN EN 60715
Surface finish	galvanized, chromium-plated	Basic material	Steel
Integral fixing	Screwed		

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		