


RS VERT SUPPLY BLL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Energy DIN rail distributor

Multiple energy distributor in the meter cabinet for the TS 35 mounting rail

- 2-pin, color-coded
- 230 V, IP 30
- Fuse protecting modules 25kA

General ordering data

Order No.	8000074943
Type	RS VERT SUPPLY BLL
GTIN (EAN)	8430243431811
Qty.	10 items

RS VERT SUPPLY BLL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	80.2 mm	Height (inches)	3.1575 inch
Width	17.9 mm	Width (inches)	0.7047 inch
Net weight	18 g		

Temperatures

Storage temperature	-40...70 °C	Operating temperature	-40...70 °C
Humidity at operating temperature	0...85% (no condensation)		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Distribution PCB connectors	BLL 5.08/03/180 (no central pin)	Supply plug-in connectors	SL 5.08HC/03/180B (no central pin)
-----------------------------	----------------------------------	---------------------------	------------------------------------

Rating data

Protection degree	IP30	Operating voltage	230 V
Maximum current per distributor connection	9.5 A	Total operating current	19 A

Insulation coordination (EN 60664-1)

Rated insulation voltage	250 V AC	Surge voltage category	III
Pollution severity	3	Pulse voltage test (1,2/50 µs)	6 kV

Connection field

Type of connection	Plug-in connection
--------------------	--------------------

Supply connection

Type of connection	Plug-in connection
--------------------	--------------------

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

RS VERT SUPPLY BLL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

