

**WINDOW SET 330X190**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

---

**General ordering data**

Version	Klippon TB (Terminal Box), Window, Height: 330 mm, Width: 190 mm, Depth: 4 mm, Basic material: Polycarbonate
Order No.	<a href="#">8000081762</a>
Type	WINDOW SET 330X190
GTIN (EAN)	4064675855880
Qty.	50 items

## WINDOW SET 330X190

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	330 mm	Height (inches)	12.9921 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	28.92 g		

### Temperatures

Operating temperature	-35 °C...90 °C
-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

### General information

Material thickness	4 mm	Operating temperature, max.	90 °C
Operating temperature, min.	-35 °C	UL 94 flammability rating	V-0
Standards	EN 45545-2:2020	Impact resistance	IK08
Protection degree	IP66	Basic material	Polycarbonate

### General information on accessories

Material thickness	4 mm	Basic material	Polycarbonate
--------------------	------	----------------	---------------

### Classifications

ETIM 8.0	EC002498	ETIM 9.0	EC002498
ETIM 10.0	EC002498	ECLASS 14.0	27-37-13-92
ECLASS 15.0	27-37-13-92		