

**KTB GP 76XX15V CD S4 PE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Order No.	8000114902
Type	<a href="#">KTB GP 76XX15V CD S4 PE</a>
GTIN (EAN)	4099986797437
Qty.	1 items

**KTB GP 76XX15V CD S4 PE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.1181 inch
Height	345 mm	Height (inches)	13.5826 inch
Width	117 mm	Width (inches)	4.6063 inch
Net weight	967.4 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Material thickness	3 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404 (316L)
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	left, right	Flange plate	Yes
Areas of use	Process industry		

**General information on accessories**

Material thickness	3 mm	Solder eyelet hole diameter (D)	7 mm
Surface finish	electropolished	Basic material	Stainless steel 1.4404 (316L)

**Housing earth**

Flange plate earthing	Welded-on M6 x 10 stainless-steel earth stud
-----------------------	--

**Classifications**

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		