

KTB MOPL 5040 S2N H**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Mounting plates

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Version	Klippon TB (Terminal Box), Mounting plate, Height: 453 mm, Width: 345 mm, Depth: 1.5 mm, Basic material: Stainless steel 1.4301 (304), untreated, silver
Order No.	8000115905
Type	KTB MOPL 5040 S2N H
GTIN (EAN)	4099986782945
Qty.	1 items

KTB MOPL 5040 S2N H

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	453 mm	Height (inches)	17.8346 inch
Width	345 mm	Width (inches)	13.5826 inch
Mounting dimension - height	218.5 mm	Mounting dimension - width	329 mm
Net weight	1850 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Material thickness of flange	3 mm	Material thickness of enclosure	1.5 mm
Material thickness	1.5 mm	Installation advice	Mounting plate
Surface finish	untreated	Protection degree	with corresponding enclosure
Basic material	Stainless steel 1.4301 (304)		

General information on accessories

Material thickness	1.5 mm	Surface finish	untreated
Basic material	Stainless steel 1.4301 (304)	Mounting dimension - width	329 mm
Mounting dimension - height	218.5 mm		

Classifications

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		