


PV 112SXFXXV101TXPX15PWW
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


Standard portfolio for Multi MPPT string inverters
 Protect strings and inverters against overvoltage.
 Protecting long cables and string inverter inputs (MPPT's)
 is crucial for the smooth operation of solar plant installations whether it's a rooftop or utility scale one. For that purpose, Weidmueller has developed a product portfolio with a set of different cabinets which helps to protect the cables and/or the string DC input side of the inverter against potential overvoltages. These solutions allow installers and developers to benefit from Weidmueller's experience in solar PV and its commitment with quality standards. Multi-MMPT

General ordering data

Version	Photovoltaics, Assembled enclosure, Combiner Box, 1500 V, Surge protection I / II, WM4C, for wall mounting, Portrait, String Inverter, 6 MPP's
Order No.	8000126354
Type	PV 112SXFXXV101TXPX15PWW
GTIN (EAN)	4099986906259
Qty.	1 items

PV 112SXFXCXXV101TXPX15PWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	530 mm	Height (inches)	20.8661 inch
Width	430 mm	Width (inches)	16.9291 inch
Net weight	12529.05 g		

Temperatures

Ambient temperature -20 °C...45 °C Operating temperature -20°C to +45°C

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

DC electrical properties

Rated voltage	1500 V	Earthing	Directly at the VPU
Surge protection DC side	1500 V type I+II with remote contact		

DC inputs

Number of DC inputs	12		
Connection type, DC input cable	WM4C plug-in connector		
Connection DC input cable (-)	WM4C plug-in connector		
Amount of maximum power points (MPP)	6		
Functional earth connector	Cable entry	Number of cable entries	1
		Cable diameter, min.	6 mm
		Cable diameter, max.	12 mm
	Wire connection	Type of connection	Screw connection
Number of inputs	12		
Number of conduit inlets	1		
Connection DC input cable (+)	WM4C plug-in connector		
Fuse type	Neither fuse cartridge nor holder		
Type of fuse	Neither fuse cartridge nor holder		

DC outputs

DC output cable connection	WM4C plug-in connector	Connection type, DC output cable	WM4C plug-in connector
Number of DC outputs	12		

DC string monitoring

Monitoring function Non monitored

PV 112SFXCXXV101TXPX15PWW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Housing**

Type of mounting	Wall mounting	Protection degree	IP65
------------------	---------------	-------------------	------

Norms and standards

Standards	IEC 61439-2 ed 3.0, EN 61439-2:2020
-----------	-------------------------------------

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 8.0	EC003857	ETIM 9.0	EC003857
ETIM 10.0	EC003857	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

