

MBGE ADAPTER SLC-500 RT26**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Adapters for migration – SLC500.

The front adapters with pre-assembled cables provide a safe migration from the SLC500 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000128582
Type	MBGE ADAPTER SLC-500 RT26
GTIN (EAN)	4099986919655
Qty.	1 items

MBGE ADAPTER SLC-500 RT26

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	34.3 mm	Depth (inches)	1.3504 inch
Height	101.6 mm	Height (inches)	4 inch
Width	83.2 mm	Width (inches)	3.2756 inch
Net weight	110 g		

Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	40 A	Rated voltage UN	250 V

Connection data

Number of poles (control side)	12-pole	Connection (field side)	SL 5.08HC
--------------------------------	---------	-------------------------	-----------

Connection data

Connection (field side)	SL 5.08HC	Connection to PLC	New PLC terminal block or hardwired
-------------------------	-----------	-------------------	-------------------------------------

Ratings data

Operating voltage	250 V	Max. current per channel	7 A
Total operating current	40 A		

Insulation coordination (EN50178)

Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.5 kV	Insulation test voltage AC	1.35 kV

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MBGE ADAPTER SLC-500 RT26

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

