

## METEOSENSE LOG 2000 TCP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

|            |   |
|------------|---|
| Version    | Photovoltaics, AutomationController, Web-based, u-control 2000 web, integrated engineering tools: u-create web for PLC - (real-time system) & IIoT applications and CODESYS (u-OS) compatible |
| Order No.  | <a href="#">8000161982</a>  |
| Type       | METEOSENSE LOG 2000 TCP   |
| GTIN (EAN) | 4099987589611   |
| Qty.       | 1 items   |

## METEOSENSE LOG 2000 TCP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|                             |        |                 |             |
|-----------------------------|--------|-----------------|-------------|
| Depth                       | 76 mm  | Depth (inches)  | 2.9921 inch |
| Height                      | 120 mm | Height (inches) | 4.7244 inch |
| Width                       | 52 mm  | Width (inches)  | 2.0472 inch |
| Mounting dimension - height | 128 mm | Net weight      | 241 g       |

### Communications

|           |                                  |
|-----------|----------------------------------|
| Interface | 2x Ethernet TCP/IP, 1x Micro USB |
|-----------|----------------------------------|

### General data

|                   |      |
|-------------------|------|
| Protection degree | IP20 |
|-------------------|------|

### Output connection

|                    |         |
|--------------------|---------|
| Type of connection | PUSH IN |
|--------------------|---------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000236    | ETIM 9.0    | EC000236    |
| ETIM 10.0   | EC000236    | ECLASS 14.0 | 27-24-22-07 |
| ECLASS 15.0 | 27-24-22-07 |             |             |