

MIBRIDGE ADAPTER B, 11 POLE IPC FLT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Adapters for migration – IPC 621.

The front adapters with pre-assembled cables provide a safe migration from the IPC 621 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000168695
Type	MIBRIDGE ADAPTER B, 11 POLE IPC FLT
GTIN (EAN)	4099987803533
Qty.	ST

MIBRIDGE ADAPTER B, 11 POLE IPC FLT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	35.3 mm	Depth (inches)	1.3898 inch
Height	106 mm	Height (inches)	4.1732 inch
Width	30.6 mm	Width (inches)	1.2047 inch
Net weight	1000 g		

Temperatures

Operating temperature	-20...50 °C
-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	20 A	Rated voltage UN	250 V

Connection data

Number of poles (control side)	11-pole	Connection (field side)	IPC 621 11 pole connector
--------------------------------	---------	-------------------------	---------------------------

Connection data

Connection (field side)	IPC 621 11 pole connector	Connection to PLC	New PLC terminal block or hardwired
Number of poles (field side)	11 P		

Ratings data

Operating voltage	250 V	Max. current per channel	6 A
Total operating current	20 A		

Insulation coordination (EN50178)

Rated insulation voltage	300 V	Surge voltage category	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	2.5 kV
Insulation test voltage AC	1.8 kV	Storage temperature, min.	-20 °C
Storage temperature, max.	70 °C		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MIBRIDGE ADAPTER B, 11 POLE IPC FLT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

