



Similar to illustration

The pre-assembled control cables have pluggable 10- or 40-pole socket blocks according to IEC 603/1 DIN 41 651. They can be used to connect the PLC front adapter to the active or passive Weidmüller interfaces. They are available in different lengths.

General ordering data

Version	Pre-assembled cable, FBK, FLAT CABLE CONECTOR HE10 10P
Order No.	8235380000
Type	FBK 10/200 RK
GTIN (EAN)	4008190264604
Qty.	1 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 127 g

Temperatures

Storage temperature -10...70 °C Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General Data

Cable length	2 m	Suitable for	Digital signals
Basic material	PVC	Cable	Cable LiYY
Interface connector	FLAT CABLE CONECTOR HE10 10P	Number of poles, min.	10-pole
Connector PLC side	FLAT CABLE CONECTOR HE10 10P	Wire cross-section	0.14 mm ²

Electrical Data

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	< 50 V AC, ≤ 50 V DC	Resistance	55 mΩ/m

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		