

## POS-4P M12 M20 150MM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

### General ordering data

Version	Locating plug-in connector, M12, pin, straight, Number of poles: 4
Order No.	<a href="#">8425930000</a>
Type	POS-4P M12 M20 150MM
GTIN (EAN)	4032248119844
Qty.	1 items

## POS-4P M12 M20 150MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	65 g
------------	------

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

### Technical specifications for cable

Cable length	0.15 m	Sheathing colour	silver
Core cross-section	1.5 mm <sup>2</sup>	Shielded	No
Halogen	No	Insulation	not available
Sheath material	Nickel-plated CuZn	Colour coding	brown, blue, black
Number of poles	4		

### Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	LED	No
Housing main material	CuZn, nickel-plated	Nominal voltage	250 V
Nominal current	4 A	Protection degree	IP67
Cable gland	M 20	Temperature range of housing	-40 ... +85 ° C

### General data

Number of poles	4	Cable length	0.15 m
Coding	A-coded	Connection thread	M12
Contact surface	Gold-plated	Sheathing colour	silver
Core cross-section	1.5 mm <sup>2</sup>	Housing main material	CuZn, nickel-plated
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67	Cable gland	M 20
Basic material	Cu Zn	Fire behaviour	V2
Connection 1	M12	Connection 2	Flying wires
Sheath material	Nickel-plated CuZn	Temperature range of housing	-40 ... +85 ° C
Conductor O.D.	-		

### Classifications



ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

## POS-4P M12 M20 150MM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Drawings

[www.weidmueller.com](http://www.weidmueller.com)



## Pole scheme