


SRC 1CO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

General ordering data

Version	RIDERSERIES RCL, Relay socket, Number of contacts: 1, CO contact, Screw connection
Order No.	8690840000
Type	SRC 1CO
GTIN (EAN)	4032248361526
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2025-06-30T00:00:00+02:00
Alternative product	CSL S 2CO

SRC 1CO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223759

Dimensions and weights

Depth	61 mm	Depth (inches)	2.4016 inch
Height	77 mm	Height (inches)	3.0315 inch
Width	15.5 mm	Width (inches)	0.6102 inch
Net weight	39.9 g		

Temperatures

Storage temperature	-40 °C...70 °C	Ambient temperature	-40 °C...70 °C
Operating temperature		Humidity	40 °C / 93 % rel. humidity, no condensation

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

Load side

Contact type	1 CO contact
--------------	--------------

General data

Mounting rail	TS 35	Colour	black
---------------	-------	--------	-------

Insulation coordination

Dielectric strength, Input/Output	2.5 kVeff / 1 Min.	Dielectric strength of neighbouring contacts	2.5 kVeff / 1 Min.
Protection degree	IP20		

Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

Connection data

Wire connection method	Screw connection	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.8 Nm	Blade size	size PH1
Pitch in mm (P)	3.50 mm		

Technical data

Classifications

ETIM 8.0	EC001456	ETIM 9.0	EC001456
ETIM 10.0	EC001456	ECLASS 14.0	27-37-16-03
ECLASS 15.0	27-37-16-03		

SRC 1CO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

RCL

General ordering data

Type	SRC CLIP LP	Version
Order No.	8691090000	RIDERSERIES RCL, Retaining clip
GTIN (EAN)	4032248361793	
Qty.	10 ST	
Type	SRC CLIP HP	Version
Order No.	8691070000	RIDERSERIES RCL, Retaining clip
GTIN (EAN)	4032248361755	
Qty.	10 ST	
Type	RIM 3 110/230VUC	Version
Order No.	8691030000	RIDERSERIES RCL, LED module, Rated control voltage: 110...230 V
GTIN (EAN)	4032248361717	UC, Plug-in connection
Qty.	10 ST	
Type	RIM 3 110/230VUC GN	Version
Order No.	8713770000	RIDERSERIES RCL, LED module, Rated control voltage: 110...230 V
GTIN (EAN)	4032248390144	UC, Plug-in connection
Qty.	10 ST	
Type	RIM 3 24/60VUC	Version
Order No.	8691020000	RIDERSERIES RCL, LED module, Rated control voltage: 24...60 V UC,
GTIN (EAN)	4032248361700	Plug-in connection
Qty.	10 ST	
Type	RIM 3 24/60VUC GN	Version
Order No.	8713760000	RIDERSERIES RCL, LED module, Rated control voltage: 24...60 V UC,
GTIN (EAN)	4032248390137	Plug-in connection
Qty.	10 ST	
Type	RIM 3 6/24VUC	Version
Order No.	8691010000	RIDERSERIES RCL, LED module, Rated control voltage: 6...24 V UC,
GTIN (EAN)	4032248361694	Plug-in connection
Qty.	10 ST	
Type	RIM 3 6/24VUC GN	Version
Order No.	8713750000	RIDERSERIES RCL, LED module, Rated control voltage: 6...24 V UC,
GTIN (EAN)	4032248390120	Plug-in connection
Qty.	10 ST	

SRC 1CO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Individual components



Relay modules with forcibly guided contacts

Relays with forcibly guided contacts have a 99 % diagnostics coverage and an excellent reputation for use in safety systems. The contacts interlock mechanically with each other in order to ensure a synchronous switching status of both contacts. This guarantees that the alert contact will maintain the same switching status in the event of an error (for example, if the working contact welds from an overload). The controller (or safety controller) detects the alert contact and then compares the set values and actual values. If a difference occurs, measures can then be taken to protect equipment and human life.

- 2 CO contacts with 6 A, forcibly guided according to EN 61810-3 type B
- Proven component in safety technology
- Diagnosis coverage of 99 %

General ordering data

Type	RIM 2 6/24VDC GN	Version
Order No.	8713720000	RIDERSERIES FG, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248389872	voltage: 6...24 V DC, Plug-in connection
Qty.	10 ST	

RCL

General ordering data

Type	RIM 2 6/24VDC	Version
Order No.	8690950000	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248361632	voltage: 6...24 V DC, Plug-in connection
Qty.	10 ST	
Type	RIM 2 24/60VDC GN	Version
Order No.	8713730000	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248389889	voltage: 24...60 V DC, Plug-in connection
Qty.	10 ST	
Type	RIM 2 24/60VDC	Version
Order No.	8690960000	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248361649	voltage: 24...60 V DC, Plug-in connection
Qty.	10 ST	
Type	RIM 4 6/24VUC GN	Version
Order No.	8713780000	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390151	voltage: 6...24 V UC, Plug-in connection
Qty.	10 ST	

SRC 1CO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	RIM 4 6/24VUC	Version
Order No.	8691040000	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248361724	voltage: 6...24 V UC, Plug-in connection
Qty.	10 ST	
Type	RIM 4 110/230VUC GN	Version
Order No.	8713800000	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390182	voltage: 110...230 V UC, Plug-in connection
Qty.	10 ST	
Type	RIM 4 110/230VUC	Version
Order No.	8691060000	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248361748	voltage: 110...230 V UC, Plug-in connection
Qty.	10 ST	
Type	RIM 4 24/60VUC GN	Version
Order No.	8713790000	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390168	voltage: 24...60 V UC, Plug-in connection
Qty.	10 ST	
Type	RIM 3 110/230VAC	Version
Order No.	8691000000	RIDERSERIES RCL, RC filter, Rated control voltage: 110...230 V AC,
GTIN (EAN)	4032248361687	Plug-in connection
Qty.	10 ST	
Type	RIM 1 6/230V	Version
Order No.	8690940000	RIDERSERIES RCL, Free-wheeling diode, Rated control voltage: 6...
GTIN (EAN)	4032248361601	230 V, Plug-in connection
Qty.	10 ST	

Individual components



Relay modules with forcibly guided contacts

Relays with forcibly guided contacts have a 99 % diagnostics coverage and an excellent reputation for use in safety systems. The contacts interlock mechanically with each other in order to ensure a synchronous switching status of both contacts. This guarantees that the alert contact will maintain the same switching status in the event of an error (for example, if the working contact welds from an overload). The controller (or safety controller) detects the alert contact and then compares the set values and actual values. If a difference occurs, measures can then be taken to protect equipment and human life.

- 2 CO contacts with 6 A, forcibly guided according to EN 61810-3 type B
- Proven component in safety technology
- Diagnosis coverage of 99 %

General ordering data

Type	SRC MARK	Version
Order No.	8693270000	RIDERSERIES FG, Label
GTIN (EAN)	4032248364725	
Qty.	10 ST	

Accessories

RCL

General ordering data

Type	SRC CLIP HM	Version
Order No.	8693370000	RIDERSERIES FG, Retaining clip
GTIN (EAN)	4032248364817	
Qty.	10 ST	