

MI-A-PSM24VDC


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Specific adapter to be connected to the MICROSERIE RELAYS using a 10-pole flat-cable connector or 15-pole Sub-D connector.

General ordering data

Version	Adapter, MICRO-Interface, IEC 60603/DIN41612 plug-in connectors, Screw connection
Order No.	8800230000
Type	MI-A-PSM24VDC
GTIN (EAN)	4032248497171
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-10T00:00:00+01:00

MI-A-PSM24VDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	98 mm	Height (inches)	3.8583 inch
Width	88 mm	Width (inches)	3.4646 inch
Net weight	32 g		

Temperatures

Storage temperature	-20...85 °C	Operating temperature	0...50 °C
---------------------	-------------	-----------------------	-----------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Supply voltage	max. 30 V AC/DC
----------------	-----------------

Ratings data

Operating voltage	30 V UC	Max. current per channel	0.5 A
Total operating current	2 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.35 kV		

Supply connection

Type of connection	Screw connection
--------------------	------------------

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

Drawings

Electric symbol

