

IE-S-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Junction box, design for SnapIn plug-in connectors ver.6
according to IEC 61076-3-106, plastic

General ordering data

Version	Connecting plug, Junction box, IP67, Cat.6A / Class EA (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	8808370000
Type	IE-S-IP67
GTIN (EAN)	403224850595 1
Qty.	1 items

IE-S-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 90 g

Temperatures

Storage temperature Installation temperature Operating temperature -40 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	Protection degree	IP67
Plugging cycles	750	Composition	Screw-on junction box including RJ45 module with IDC connection
Wiring	EIA/TIA T568 A, EIA/TIA T568 B		

General standards

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6

Technical data RJ45 module

Wiring EIA/TIA T568 A, EIA/TIA T568 B

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing

