

IE-CT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Version	Continuity tester for data cables
Order No.	8808420000
Type	IE-CT
GTIN (EAN)	4032248506002
Qty.	1 items

IE-CT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	36 mm	Height (inches)	1.4173 inch
Width	70 mm	Width (inches)	2.7559 inch
Length	140 mm	Length (inches)	5.5118 inch
Net weight	348.48 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Measuring and testing devices

Supply	9V battery	Display	digital
--------	------------	---------	---------

Classifications

ETIM 8.0	EC002080	ETIM 9.0	EC002080
ETIM 10.0	EC002080	ECLASS 14.0	27-20-11-08
ECLASS 15.0	27-20-11-08		