

## IE-XM-6U-RJ45/RJ45-IP67

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



SnapIn plug-in connectors according to IEC 61076-3-106  
ver.6 in plastic, with RJ45 insert

### General ordering data

Version	Mounting flange, Coupling flange, 90° up, Cat.6 (ISO/IEC 11801), IP67
Order No.	<a href="#">8829440000</a>
Type	IE-XM-6U-RJ45/RJ45-IP67
GTIN (EAN)	4032248532469
Qty.	1 items

## IE-XM-6U-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 50 g

## Temperatures

Storage temperature Operating temperature -40 °C...70 °C  
Installation temperature

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## General data

Connection 1	RJ45	Connection 2	RJ45 90°;
Description of article	Coupling flange, 90° up	Composition	Installation flange with mounting frame and RJ45 module, socket-socket 90°, upwards captive lid
Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Category	Cat.6 (ISO/IEC 11801)	Contact surface	Gold over nickel
Type of mounting	Cabinet, Distribution box	Shielding	360°; shield contact
Protection degree	IP67	Plugging cycles	750

## Electrical properties

Dielectric strength, contact / shield  $\geq 1500$  V AC/DC Dielectric strength, contact / contact  $\geq 1000$  V AC/DC

## General standards

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6, IEC 60603-7-5

## Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**IE-XM-6U-RJ45/RJ45-IP67**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**

