

IE-XM-USB/USB-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



SnapIn plug-in connectors according to IEC 61076-3-106
ver.6 in plastic, with USB insert

General ordering data

Version	Mounting flange, USB flange, Cat.6 (ISO/IEC 11801), IP67
Order No.	8892670000
Type	IE-XM-USB/USB-IP67
GTIN (EAN)	4032248641123
Qty.	1 items

IE-XM-USB/USB-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	37 g
------------	------

Temperatures

Storage temperature	Operating temperature	-20 °C...85 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General Info

Connection 1	USB	Connection 2	USB
Description of article	USB flange	Colour	Light Grey
Housing main material	PA 66, UL 94: V-0	Category	Cat.6 (ISO/IEC 11801)
Type of mounting	Cabinet, Distribution box	Shielding	360° shield contact
Protection degree	IP67	Plugging cycles	750

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

IE-XM-USB/USB-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing

