

WIDERSTANDSBOX 8X18K 3W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product is no longer available, Data sheet for information only



General ordering data

Order No.	8943120000
Type	WIDERSTANDSBOX 8X18K 3W
GTIN (EAN)	4032248752713
Qty.	1 items
Delivery status	Discontinued
Available until	2024-06-04T00:00:00+02:00

WIDERSTANDSBOX 8X18K 3W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Width	55.5 mm	Width (inches)	2.185 inch
Length	125 mm	Length (inches)	4.9212 inch
Net weight	425 g		

Temperatures

Storage temperature	-40...70 °C	Ambient temperature	...70 °C
Operating temperature	-25...70		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Type of connection	Tension-clamp connection	Type of component	Resistance
--------------------	--------------------------	-------------------	------------

Insulation coordination (EN50178)

Pollution severity level	2
--------------------------	---

Connection field

Type of connection	Tension-clamp connection	Stripping length	7 mm
Clamping range, max.	1 mm ²	Clamping range, min.	0.08 mm ²

Input

Resistance	8 x 3,6 kΩ 1 W
------------	----------------

Connection data

Type of connection	Tension-clamp connection
--------------------	--------------------------

Classifications

ETIM 8.0	EC002024
----------	----------