

IE-TO-LCD-MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Mounting rail outlet, LC duplex junction design according to IEC 61754-20

General ordering data

Version	Mounting rail outlet, fibre-optic, LC Duplex, Multi-mode, GOF, POF, IP20
Order No.	8947010000
Type	IE-TO-LCD-MM
GTIN (EAN)	4032248735020
Qty.	10 items

IE-TO-LCD-MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	32.5 g
------------	--------

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a
REACH SVHC	Lead 7439-92-1

General data

Colour	Light Grey	Housing main material	PA UL 94 V0
Type of mounting	TS 35	Protection degree	IP20
Plugging cycles	1000	Fibre type	Multimode, GOF, POF
Insertion loss	≤ 0.4 dB	Connection 1	LC Duplex
Connection 2	LC Duplex		

General standards

Connector standard	IEC 61754-20
--------------------	--------------

Classifications

ETIM 8.0	EC000313	ETIM 9.0	EC000313
ETIM 10.0	EC000313	ECLASS 14.0	27-44-03-20
ECLASS 15.0	27-44-03-20		

Drawings

Dimensioned drawing

