

## IE-TO-LCD-SM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Mounting rail outlet, LC duplex junction design according to IEC 61754-20

### General ordering data

Version	Mounting rail outlet, fibre-optic, LC Duplex, Single-mode, IP20
Order No.	<a href="#">8947020000</a>
Type	IE-TO-LCD-SM
GTIN (EAN)	4032248735037
Qty.	10 items

## IE-TO-LCD-SM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	30.1 g
------------	--------

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a
REACH SVHC	Lead 7439-92-1

### General data

Colour	Light Grey	Housing main material	PA UL 94 V0
Type of mounting	TS 35	Protection degree	IP20
Plugging cycles	1000	Fibre type	Singlemode
Insertion loss	≤ 0.5 dB	Connection 1	LC Duplex
Connection 2	LC Duplex		

### General standards

Connector standard	IEC 61754-20
--------------------	--------------

### Classifications

ETIM 8.0	EC000313	ETIM 9.0	EC000313
ETIM 10.0	EC000313	ECLASS 14.0	27-44-03-20
ECLASS 15.0	27-44-03-20		

Drawings

Dimensioned drawing

