

M-D-STRIPAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9001280000
Type	M-D-STRIPAX
GTIN (EAN)	4008190011215
Qty.	1 items

M-D-STRIPAX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	82 mm	Width (inches)	3.2283 inch
Net weight	107.36 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping tool for up to 1 mm ² for PVC/silicone
------------------------	---

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Max. conductor diameter	1.3 mm
Min. conductor diameter	0.3 mm	Stripping range AWG, max.	18 AWG
Stripping range AWG, min.	28 AWG	Stripping range, min.	0.08 mm ²
Stripping length, max.	7 mm	Conductor cross-section, max.	1 mm ²
Conductor cross-section, min.	0.08 mm ²		

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

Drawings

Example of use

