

## KT ZQV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

### General ordering data

Version	Cutting tool for one-hand operation
Order No.	<a href="#">9002170000</a>
Type	KT ZQV
GTIN (EAN)	4032248291670
Qty.	1 items

## KT ZQV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	12 mm	Depth (inches)	0.4724 inch
Height	44 mm	Height (inches)	1.7323 inch
Width	208 mm	Width (inches)	8.189 inch
Net weight	280.78 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

### Technical data

Description of article	Cutting tool for clean cutting of Weidmüller Z-Series cross-connections	Version	One-hand mechanical
------------------------	---	---------	---------------------

### Cutting tools

Copper cable - solid, max. (AWG)	2 AWG	Copper cable - solid, max.	35 mm <sup>2</sup>
Copper cable - flexible, max. (AWG)	6 AWG	Copper cable - flexible, max.	16 mm <sup>2</sup>
Copper cable - stranded, max. (AWG)	2/0 AWG	Copper cable - stranded, max.	70 mm <sup>2</sup>
Copper cable, max. diameter	14 mm		

### Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		