

KT ZQV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9002170000
Type	KT ZQV
GTIN (EAN)	4032248291670
Qty.	1 items

KT ZQV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12 mm	Depth (inches)	0.4724 inch
Height	44 mm	Height (inches)	1.7323 inch
Width	208 mm	Width (inches)	8.189 inch
Net weight	280.78 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Cutting tool for clean cutting of Weidmüller Z-Series cross-connections	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Copper cable - solid, max. (AWG)	2 AWG	Copper cable - solid, max.	35 mm ²
Copper cable - flexible, max. (AWG)	6 AWG	Copper cable - flexible, max.	16 mm ²
Copper cable - stranded, max. (AWG)	2/0 AWG	Copper cable - stranded, max.	70 mm ²
Copper cable, max. diameter	14 mm		

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		