

KT-F 36**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Suitable in situations where cables have to be cut in confined spaces
- Easy handling
- Minimal manual force required
- Release option in every cutting position
- Not suitable for steel wires, steel-armoured cables, aluminium alloys and hard-drawn copper conductors
- Do not cut live conductors

General ordering data

Version	Cutting tools, Front cutter
Order No.	9002190000
Type	KT-F 36
GTIN (EAN)	4008190066345
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2024-06-06T00:00:00+02:00

KT-F 36

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	150 mm	Height (inches)	5.9055 inch
Width	360 mm	Width (inches)	14.1732 inch
Net weight	1642.78 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1

Technical data

Description of article	Front cable cutter for up to 35 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Cable type	Copper and aluminium cables	Copper cable - flexible, max. (kcmil)	600 kcmil
Copper cable - flexible, max.	300 mm ²	Copper cable - stranded, max. (kcmil)	600 kcmil
Copper cable - stranded, max.	300 mm ²	Copper cable, max. diameter	35 mm
Max. conductor diameter	36 mm	Stranded aluminium cable, max. (kcmil)	600 kcmil
Stranded aluminium cable, max (mm ²)	300 mm ²	Stranded aluminium cable, max. diameter	35 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Drawings

 max. 20 mm

 max. 16 mm²

 max. 35 mm²

 max. 70 mm²