

M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

| | |
|------------|-----------------------------------|
| Version | Tools, Stripping and cutting tool |
| Order No. | 9003500000 |
| Type | M-D-STRIPAX +6 MEHA |
| GTIN (EAN) | 4008190107109 |
| Qty. | 1 items |

M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 16 mm | Depth (inches) | 0.6299 inch |
| Height | 135 mm | Height (inches) | 5.3149 inch |
| Width | 82 mm | Width (inches) | 3.2283 inch |
| Net weight | 106.38 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

Technical data

| | |
|------------------------|--------------------------------------|
| Description of article | Stripping tool with 6 sets of blades |
|------------------------|--------------------------------------|

Stripping tools

| | | | |
|-------------------------------|----------------------------------|-------------------------------|----------------------|
| Cable type | Conductor with custom insulation | Max. conductor diameter | 1.3 mm |
| Min. conductor diameter | 0.2 mm | Stripping range AWG, max. | 18 AWG |
| Stripping range AWG, min. | 32 AWG | Stripping length, max. | 7 mm |
| Conductor cross-section, max. | 0.82 mm ² | Conductor cross-section, min. | 0.03 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002109 | ETIM 9.0 | EC002109 |
| ETIM 10.0 | EC002109 | ECLASS 14.0 | 21-04-37-06 |
| ECLASS 15.0 | 21-04-37-06 | | |

M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

