

## MEHA KP RT M-D-SPX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

### General ordering data

|            |                             |
|------------|-----------------------------|
| Version    | Accessories, Set of cutters |
| Order No.  | <a href="#">9003610000</a>  |
| Type       | MEHA KP RT M-D-SPX          |
| GTIN (EAN) | 4008190058272               |
| Qty.       | 1 items                     |

**MEHA KP RT M-D-SPX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 16 mm   | Depth (inches)  | 0.6299 inch |
| Height     | 11.5 mm | Height (inches) | 0.4528 inch |
| Width      | 26 mm   | Width (inches)  | 1.0236 inch |
| Length     | 26 mm   | Length (inches) | 1.0236 inch |
| Net weight | 3.68 g  |                 |             |

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected          |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Technical data**

|                        |   |
|------------------------|---|
| Description of article | Set of blades for Mini-Duro-Stripax up to AWG 24 for PTFE |
|------------------------|---|

**Stripping tools**

|                         |                                  |                         |        |
|-------------------------|----------------------------------|-------------------------|--------|
| Cable type              | Conductor with custom insulation | Max. conductor diameter | 0.5 mm |
| Min. conductor diameter | 0.3 mm                           | Stripping length, max.  | 7 mm   |
| Stripping length, min.  | 3 mm                             | Colour                  | red    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001509    | ETIM 9.0    | EC001509    |
| ETIM 10.0   | EC001509    | ECLASS 14.0 | 21-04-48-91 |
| ECLASS 15.0 | 21-04-48-91 |             |             |