

## M-D-STRIPAX LWL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

### General ordering data

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9003750000</a>
Type	M-D-STRIPAX LWL
GTIN (EAN)	4008 190068042
Qty.	1 items

**M-D-STRIPAX LWL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	16 mm	Depth (inches)	0.6299 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	82 mm	Width (inches)	3.2283 inch
Net weight	96.73 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Technical data**

Description of article	Stripping tool for fibre-optic cables
------------------------	---------------------------------------

**Stripping tools**

Cable type	POF conductor with an inner conductor of 1 mm	Max. conductor diameter	1 mm
Stripping range AWG, max.	18 AWG	Stripping length, max.	7.5 mm
Colour	grey	Conductor cross-section, max.	0.78 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

## M-D-STRIPAX LWL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Accessories / replacement parts



- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

### General ordering data

Type	MEHA KP LWL M-D-SPX	Version	
Order No.	<a href="#">9003760000</a>	Accessories, Spare cutting blade	
GTIN (EAN)	4008190055110		
Qty.	1 ST		