

M-D-STRIPAX LWL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9003750000
Type	M-D-STRIPAX LWL
GTIN (EAN)	4008 190068042
Qty.	1 items

M-D-STRIPAX LWL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	82 mm	Width (inches)	3.2283 inch
Net weight	96.73 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping tool for fibre-optic cables
------------------------	---------------------------------------

Stripping tools

Cable type	POF conductor with an inner conductor of 1 mm	Max. conductor diameter	1 mm
Stripping range AWG, max.	18 AWG	Stripping length, max.	7.5 mm
Colour	grey	Conductor cross-section, max.	0.78 mm ²

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

M-D-STRIPAX LWL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

General ordering data

Type	MEHA KP LWL M-D-SPX	Version	
Order No.	9003760000	Accessories, Spare cutting blade	
GTIN (EAN)	4008190055110		
Qty.	1 ST		