

## H16,0/25

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

### General ordering data

Version	Wire-end ferrule, Standard, 25 mm, 25 mm, No
Order No.	<a href="#">9004150000</a>
Type	H16,0/25
GTIN (EAN)	4008190037253
Qty.	100 items
Packaging	loose

## H16,0/25

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

### Dimensions and weights

Net weight	0.73 g
------------	--------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

### Wire-end ferrules

Contact surface diameter (D1)	5.8 mm	Contact surface length (L2)	25 mm
Collar diameter (D2)	7.5 mm	L1 in mm	25.00 mm
Wire connection cross section AWG, max.	AWG 6	Stripping length	25 mm
Conductor cross-section	16 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

