

## H70,0/32

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



- For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in poly-bag

### General ordering data

Version	Wire-end ferrule, Standard, 32 mm, 32 mm, No
Order No.	<a href="#">9004240000</a>
Type	H70,0/32
GTIN (EAN)	4008190131395
Qty.	50 items
Packaging	loose

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

**Dimensions and weights**

Net weight	4.57 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	Wire end ferrule without plastic collar, (2)Wire-end ferrule	Version	Standard
------------------------	--------------------------------------------------------------	---------	----------

**Wire-end ferrules**

Contact surface diameter (D1)	12.5 mm	Contact surface length (L2)	32 mm
Collar diameter (D2)	15 mm	L1 in mm	32.00 mm
Wire connection cross section AWG, max.	AWG 2/0	Stripping length	32 mm
Conductor cross-section	70 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

**Drawings**

