


H0,75/14D GR BD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
Order No.	9004300000
Type	H0,75/14D GR BD
GTIN (EAN)	4008 190154837
Qty.	500 items
Packaging	Reel packaged

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.09 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Linked wire-end ferrules, grey	Version	Standard
------------------------	--------------------------------	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	1.2 mm	Contact surface length (L2)	8 mm
Collar diameter (D2)	2.8 mm	Plastic collar thickness (S2)	0.25 mm
L1 in mm	14.00 mm	Wire connection cross section AWG, max.	AWG 18
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 005 A
Stripping length	10 mm	Conductor cross-section	0.75 mm ²
Colour code	DIN		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

