


## H1,5/14 R BD



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 10 mm, 8 mm, red |
| Order No.  | <a href="#">9004340000</a>                   |
| Type       | H1,5/14 R BD                                 |
| GTIN (EAN) | 4008 190080723                               |
| Qty.       | 500 items                                    |
| Packaging  | Reel packaged                                |

**Technical data**

**Approvals**

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E499744                    |

**Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 0.1 g |
|------------|-------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Technical data**

|                        |                               |         |          |
|------------------------|-------------------------------|---------|----------|
| Description of article | Linked wire-end ferrules, red | Version | Standard |
|------------------------|-------------------------------|---------|----------|

**Wire-end ferrules**

|                               |                     |   |             |
|-------------------------------|---------------------|---|-------------|
| Contact surface diameter (D1) | 1.7 mm              | Contact surface length (L2)             | 8 mm        |
| Collar diameter (D2)          | 3.2 mm              | Plastic collar thickness (S2)           | 0.25 mm     |
| L1 in mm                      | 14.00 mm            | Wire connection cross section AWG, max. | AWG 16      |
| Metal sleeve thickness (S1)   | 0.15 mm             | Stripping length                        | 10 mm       |
| Conductor cross-section       | 1.5 mm <sup>2</sup> | Colour code                             | Weidmueller |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

