

CTN 25 D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for non-insulated connectors
Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | |
|------------|---|
| Version | Pressing tool, Crimping tool for contacts, 10mm ² , 25mm ² , Indent crimp |
| Order No. | 9006220000 |
| Type | CTN 25 D4 |
| GTIN (EAN) | 4008 190198633 |
| Qty. | 1 items |

CTN 25 D4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|----------------|-------------|
| Width | 250 mm | Width (inches) | 9.8425 inch |
| Net weight | 653.78 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2159813b-98fd-4068-b62a-bc89a046c012 |

Technical data

| | | | |
|------------------------|---|---------|---|
| Description of article | Crimping tool for non-insulated connectors, 10-25 mm ² | Version | Mechanical, without interchangeable inserts |
|------------------------|---|---------|---|

Description of contact

| | | | |
|-----------------------------------|------------------------|-----------------------------------|--------------------|
| Type of contact | Uninsulated connection | Conductor cross-section, max. AWG | AWG 4 |
| Conductor cross-section, min. AWG | AWG 8 | Crimping range, max. | 25 mm ² |
| Crimping range, min. | 10 mm ² | | |

tool data crimping

| | | | |
|---------------------------------------|--------------------|---------------------------------|--------------------|
| Wire end ferrules cross-section, max. | 25 mm ² | Copper connector (rolled), max. | 25 mm ² |
| Copper connector (rolled), min. | 10 mm ² | Crimping type/profile | Indent crimp |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000168 | ETIM 9.0 | EC000168 |
| ETIM 10.0 | EC000168 | ECLASS 14.0 | 21-04-38-11 |
| ECLASS 15.0 | 21-04-38-11 | | |

Drawings

