

CTX 502**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	9006380000
Type	CTX 502
GTIN (EAN)	4008190123512
Qty.	1 items

CTX 502

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	654.08 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 9.3	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Hexagon spanner width (A 2)	1.75 mm	Hexagon AF (A)	9.3 mm
Wire end ferrules cross-section, max.	89 mm ²	Wire end ferrules cross-section, min.	89 mm ²
Diameter of outer sleeve	10.7 mm	Crimping station, width (B 2)	2.3 mm
Crimping station, width (B 1)	12 mm	Crimping type/profile	Hexagonal crimp
Internal contact diameter (D)	2 mm		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

