


H1,5/19,5X SW SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- In multi-pack bag
- Weidmüller colour code

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 10 mm, black
Order No.	9006630000
Type	H1,5/19,5X SW SV
GTIN (EAN)	4008 190332266
Qty.	100 items
Packaging	Multipack bag

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.23 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, black	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	1.8 mm	Contact surface length (L2)	10 mm
Collar diameter (D2)	7 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	19.50 mm	Wire connection cross section AWG, max.	AWG 16
Metal sleeve thickness (S1)	0.15 mm	Stripping length	15 mm
Conductor cross-section	1.5 mm ²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

