

LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
Order No.	9007460000
Type	LG DMS PRO/ DMS 3
GTIN (EAN)	4008190404970
Qty.	1 items

LG DMS PRO/ DMS 3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	178 mm	Depth (inches)	7.0079 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	150 mm	Width (inches)	5.9055 inch
Length	178 mm	Length (inches)	7.0079 inch
Net weight	604.79 g		

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC Lead 7439-92-1

Technical data

Voltage range	12 / 14.4 / 18 V	Description of article	Mains-operated torque screwdriver with 1/4" drive
Electrical connection	220 - 240 V / 50 - 60 Hz		

Electric screwdriver

Charger output	DC 2.8...6V; 4.8A / 30W max.	Charger input	AC 220-240V~50-60Hz 30W
Idling speed	200 u. 600 min-1	Weight	600 g
Nominal voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Battery voltage	3.6 V	Weight of charger	600 g
Max. coupling torque	3 Nm		

Classifications

ETIM 8.0	EC000359	ETIM 9.0	EC000359
ETIM 10.0	EC000359	ECLASS 14.0	21-05-29-01
ECLASS 15.0	21-05-29-01		