

DMS 3 SET 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, Mains-operated torque screwdriver
Order No.	9007480000
Type	DMS 3 SET 2
GTIN (EAN)	4008 190405298
Qty.	1 items

DMS 3 SET 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	205 mm	Depth (inches)	8.0709 inch
Height	205 mm	Height (inches)	8.0709 inch
Width	325 mm	Width (inches)	12.7952 inch
Length	78 mm	Length (inches)	3.0709 inch
Net weight	1695.76 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

Technical data

Description of article	Cordless torque screwdriver set, as set 1 but with additional rechargeable battery
------------------------	--

Electric screwdriver

Idling speed	200 u. 400 min ⁻¹	Weight	2004 g
Nominal voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Torque setting, max.	15 Nm	Torque setting, min.	15 Nm
Rechargeable batteries	Ni-Mh cells	Weight of rechargeable battery	122 g
Battery voltage	2.4 V		

Screwing tools

Torque setting, max.	15 Nm	Torque setting, min.	15 Nm
----------------------	-------	----------------------	-------

Classifications

ETIM 8.0	EC001395	ETIM 9.0	EC001395
ETIM 10.0	EC001395	ECLASS 14.0	21-05-08-90
ECLASS 15.0	21-05-08-90		

Example of use

