

SDIS 0.4X2.5X75

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Screwdriver
Order No.	9008370000
Type	SDIS 0.4X2.5X75
GTIN (EAN)	4032248056330
Qty.	1 items
Delivery status	Discontinued
Available until	2021-01-31T00:00:00+01:00
Alternative product	SDIS 0.4X2.5X75

SDIS 0.4X2.5X75

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	179 mm	Width (inches)	7.0472 inch
Diameter	23 mm	Net weight	28.5 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4x2.5x75
------------------------	--

Screwing tools

Blade width (B)	2.5 mm	Blade thickness (A)	0.4 mm
Form	Slotted	Blade length	75 mm
Blade type	A		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		