

AM ASI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Quick and accurate stripping
- No need to adjust cutting depth
- No damage to inner conductor

General ordering data

| | |
|------------|-----------------------------------|
| Version | Tools, Stripping and cutting tool |
| Order No. | 9009950000 |
| Type | AM ASI |
| GTIN (EAN) | 4032248363407 |
| Qty. | 1 items |

AM ASI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 25 mm | Depth (inches) | 0.9842 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 124 mm | Width (inches) | 4.8819 inch |
| Net weight | 48.6 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

Technical data

| | |
|------------------------|---|
| Description of article | Insulation stripping tool for rubberized ASI cables |
|------------------------|---|

Stripping tools

| | | | |
|-----------------------|---------------------|-------------------------------|---------------------|
| Cable type | ASI-EPDM | Max. conductor diameter | 1.4 mm |
| Stripping range, min. | 1.5 mm ² | Conductor cross-section, max. | 1.5 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000163 | ETIM 9.0 | EC000163 |
| ETIM 10.0 | EC000163 | ECLASS 14.0 | 21-04-90-90 |
| ECLASS 15.0 | 21-04-90-90 | | |