

HTG 58/59

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	901202000
Type	HTG 58/59
GTIN (EAN)	4008 1900 18207
Qty.	1 items

HTG 58/59

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	418.7 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC / AF 5.4/6.48	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Hexagon spanner width (A 2)	6.48 mm	Hexagon spanner width (A 3)	1.72 mm
Hexagon AF (A)	5.4 mm	Wire end ferrules cross-section, max.	30 mm ²
Wire end ferrules cross-section, min.	30 mm ²	Diameter of outer sleeve	6.2 mm
Crimping station, width (B 2)	10 mm	Crimping station, width (B 3)	2.3 mm
Crimping station, width (B 1)	10 mm	Crimping type/profile	Hexagonal crimp
Internal contact diameter (D)	2 mm		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

