

HTG 174

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	9012410000
Type	HTG 174
GTIN (EAN)	4008 190009434
Qty.	1 items

HTG 174

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	449 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 4.52	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Hexagon spanner width (A 2)	1.72 mm	Hexagon AF (A)	4.52 mm
Wire end ferrules cross-section, max.	22 mm ²	Wire end ferrules cross-section, min.	22 mm ²
Diameter of outer sleeve	5.4 mm	Crimping station, width (B 2)	2.3 mm
Crimping station, width (B 1)	10 mm	Crimping type/profile	Hexagonal crimp
Internal contact diameter (D)	2 mm		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

