

HTF 48

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for flat blade connectors and flat blade receptacles with open or rolled crimping claw

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.5mm ² , 2.5mm ² , B-Crimp
Order No.	9013080000
Type	HTF 48
GTIN (EAN)	4008190113056
Qty.	1 items

HTF 48

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	453.98 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tools for flat-blade connectors and flat-blade receptacles, connector width 4.8 mm	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	F-plug / -sleeve	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 21	Plug width	4.8 mm
Crimping range, max.	2.5 mm ²	Crimping range, min.	0.5 mm ²

tool data crimping

Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²
Crimping type/profile	B-Crimp		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

