

## HTF 28

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for flat blade connectors and flat blade receptacles with open or rolled crimping claw

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

### General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.1mm <sup>2</sup> , 1mm <sup>2</sup> , B-Crimp
Order No.	<a href="#">9013090000</a>
Type	HTF 28
GTIN (EAN)	4008 190129439
Qty.	1 items

## HTF 28

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	449.98 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

## Technical data

Description of article	Crimping tools for flat-blade connectors and flat-blade receptacles, connector width 2.8 mm	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

## Description of contact

Type of contact	F-plug / -sleeve	Conductor cross-section, max. AWG	AWG 18
Conductor cross-section, min. AWG	AWG 28	Plug width	2.8 mm
Crimping range, max.	1 mm <sup>2</sup>	Crimping range, min.	0.1 mm <sup>2</sup>

## tool data crimping

Wire end ferrules cross-section, max.	1 mm <sup>2</sup>	Crimping type/profile	B-Crimp
---------------------------------------	-------------------	-----------------------	---------

## Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

