

CTX CM 1.6/2.5 ZERT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.14mm ² , 4mm ² , W crimp
Order No.	9013690000
Type	CTX CM 1.6/2.5 ZERT
GTIN (EAN)	4032248326419
Qty.	1 items

CTX CM 1.6/2.5 ZERT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	750 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for HD, HE and ConConcept M10/M5 contacts, 0.14-4 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Turned contacts	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	4 mm ²
Crimping range, min.	0.14 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	4 mm ²	Crimping type/profile	W crimp
Crimping profile 5	4 mm ²		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

