

## HTF DFF

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for for turned/stamped contact

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

### General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.22mm <sup>2</sup> , 2.5mm <sup>2</sup> , B-Crimp
Order No.	<a href="#">901414000</a>
Type	HTF DFF
GTIN (EAN)	4008190297305
Qty.	1 items

## HTF DFF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Width	205 mm	Width (inches)	8.0709 inch
Net weight	442 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

### Technical data

Description of article	Crimping tools for Weidmüller DFF contacts	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

### Description of contact

Type of contact	Weidmüller DFF	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	2.5 mm <sup>2</sup>
Crimping range, min.	0.22 mm <sup>2</sup>		

### tool data crimping

Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.22 mm <sup>2</sup>
Crimping type/profile	B-Crimp		

### Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

