

## HTF ZRV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for for turned/stamped contact

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

### General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.2mm <sup>2</sup> , 1mm <sup>2</sup> , FoderBcrimp
Order No.	<a href="#">9014840000</a>
Type	HTF ZRV
GTIN (EAN)	4008 190949969
Qty.	1 items

## HTF ZRV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	452.7 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

### Technical data

Description of article	Crimping tools for ZRV or MKF flat-blade contacts	Version	Mechanical, without interchangeable inserts
------------------------	---------------------------------------------------	---------	---------------------------------------------

### Description of contact

Type of contact	Weidmüller ZRV	Conductor cross-section, max. AWG	AWG 17
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	1 mm <sup>2</sup>
Crimping range, min.	0.2 mm <sup>2</sup>		

### tool data crimping

Wire end ferrules cross-section, max.	1 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.2 mm <sup>2</sup>
Crimping type/profile	FoderBcrimp		

### Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

**HTF ZRV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

