

DMS 3 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, Mains-operated torque screwdriver
Order No.	9017870000
Type	DMS 3 ZERT
GTIN (EAN)	4008 190353599
Qty.	1 items

DMS 3 ZERT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	127 mm	Height (inches)	5 inch
Width	239 mm	Width (inches)	9.4094 inch
Diameter	35 mm	Net weight	472 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

Technical data

Description of article	Mains-operated torque screwdriver with 1/4" drive
------------------------	---

Electric screwdriver

Idling speed	200 u. 400 min-1	Weight	400 g
Nominal voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
Rechargeable batteries	Ni-Mh cells	Weight of rechargeable battery	122 g

Screwing tools

Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
----------------------	------	----------------------	--------

Classifications

ETIM 8.0	EC001395	ETIM 9.0	EC001395
ETIM 10.0	EC001395	ECLASS 14.0	21-05-08-90
ECLASS 15.0	21-05-08-90		

Example of use

