

## CTX CM 1.6/2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

### General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.14mm <sup>2</sup> , 4mm <sup>2</sup> , W crimp
Order No.	<a href="#">9018490000</a>
Type	CTX CM 1.6/2.5
GTIN (EAN)	4008 190884598
Qty.	1 items

## CTX CM 1.6/2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	679.78 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

### Technical data

Description of article	Crimping tool for HD, HE and ConConcept M10/M5 contacts, 0.14-4 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

### Description of contact

Type of contact	Turned contacts	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	4 mm <sup>2</sup>
Crimping range, min.	0.14 mm <sup>2</sup>		

### tool data crimping

Wire end ferrules cross-section, max.	4 mm <sup>2</sup>	Crimping type/profile	W crimp
Crimping profile 5	4 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

**Drawings**

