


H0,75/12D GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 8 mm, 6 mm, grey
Order No.	9019030000
Type	H0,75/12D GR
GTIN (EAN)	4008 190127787
Qty.	500 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.07 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, grey	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	1.2 mm	Contact surface length (L2)	6 mm
Collar diameter (D2)	2.8 mm	Plastic collar thickness (S2)	0.25 mm
L1 in mm	12.00 mm	Wire connection cross section AWG, max.	AWG 18
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 004 A
Stripping length	8 mm	Conductor cross-section	0.75 mm ²
Colour code	DIN		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

