


H4,0/26D GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 20 mm, 18 mm, grey |
| Order No. | 9019210000 |
| Type | H4,0/26D GR |
| GTIN (EAN) | 4008 190002336 |
| Qty. | 100 items |
| Packaging | loose |

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.08 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule with plastic collar, grey | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|----------|---|-------------------|
| Contact surface diameter (D1) | 2.8 mm | Contact surface length (L2) | 18 mm |
| Collar diameter (D2) | 4.8 mm | Plastic collar thickness (S2) | 0.3 mm |
| L1 in mm | 26.00 mm | Wire connection cross section AWG, max. | AWG 12 |
| Metal sleeve thickness (S1) | 0.2 mm | Military designation | T 20A 021 A |
| Stripping length | 20 mm | Conductor cross-section | 4 mm ² |
| Colour code | DIN | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

